





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R5	ADDED HEX SPEC & NOTE: 9	27MAR2025	TP	WK



1. FOR USE WITH RG-180/U,180A/U & 195/U CABLE
2. USE CRIMPING TOOL 69143
3. SEE I.S. 1771
4. MAX PANEL THICKNESS = .125
5. PRODUCT IS DESIGNED TO MEET PRODUCT SPECIFICATION 108-12013
6. PARTS PACKAGED UNASSEMBLED
7. .013X .002 DEEP IDENT GROOVE, ONLY FOR 1-330599-5
8. RESTRICTED SALES TO PROVIBTECH.
9. CRIMPING TOOL REFER TO DRAWING: 2087632



RECOMMENDED STRIP LENGTH

A	1883198-1	5-328691-0	5-328690-0	5-330598-0	6-330599-0
B	3-329049-0	-	-	330598-3	8 1-330599-5
A	329049	328691	328690	330598-2	1-330599-4
B	3-329049-0	-	-	330598-1	1-330599-3
A	3-329049-0	1-328691-2	1-328690-2	330598-1	1-330599-2
B	329049	-	-	330598	1-330599-1
A	329049	328691	328690	330598	1-330599-0
-	-	328691	328690	330598	330599
VIEW	4 FERRULE QTY=1	3 LOCKWASHER QTY=1	2 JAM NUT QTY=1	1 RECEPTACLE ASSEMBLY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -
MATERIAL SEE TABLE	FINISH -

DWN B. WERNER 07/JUL/95	CHK G. MICHAEL 13/JUL/95	APVD G. MICHAEL 13/JUL/95
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT 0.000000		
CUSTOMER DRAWING		

STE TE Connectivity

RECEPTACLE, SERIES MINIATURE THREADED				
NAME	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	A3	00779	C-330599	-
SCALE 4:1		SHEET 1 OF 1		REV R5