






PRODUCT NUMBER
SEE SHEET 2




CONFIDENTIAL

www.fciconnect.com			surface - ASME Y14.5		tolerance std - ASME Y14.5		projection 		MM 		
			TOLERANCES UNLESS		OTHERWISE SPECIFIED						
Dr	T.HOUTZ	2005-06-16	ANGULAR	LINEAR	0.X ±0.3		size	Scale			
Eng	C. H. TAN	2006-06-05			0.XX ±0.10		A2	4:1			
Chr	C. H. TAN	2007-06-04			0.XXX ±0.050			ECN ***			
Appr	JOEY NG	2007-06-04	Product family				-	Spec ref		-	
			title AirMax COVER R/A HDR & RECPT - 5pr, 2mm				dwg no 10058685		Rev. B		
			catalog no		-	CUSTOMER		sheet 1 of 2			


rev	ecn no	dr	date
A	S06-0199	CH	2006-06-05
B	S07-0055	LS	2007-06-04
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-



1		2		3	4	5	6	7	8
PART NUMBER (NOTE 3)		CONNECTOR GENDER	NUMBER OF IMLAS	DIM A	DIM C				
A	10058685-001LF	R/A HEADER	6	13.60	18.00				
	10058685-002LF	R/A HEADER	8	17.60	18.00				
	10058685-003LF	R/A HEADER	10	21.60	18.00				
	10058685-004LF	R/A RECEPT.	6	13.60	23.45				
	10058685-005LF	R/A RECEPT.	8	17.60	23.45				
	10058685-006LF	R/A RECEPT.	10	21.60	23.45				



10058685-003LF SHOWN
SCALE 4:1



10058685-006LF SHOWN
SCALE 4:1

NOTES:

1. MATERIAL: THERMOPLASTIC RESIN
COLOR : BLACK,
UL94V-0 COMPLIANT,
MAXIMUM OPERATING TEMPERATURE
IS 105°C.
2. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED
TO A MANUFACTURING SOLDER PROCESS.
3. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DESCRIBED
IN GS-22-008.
4. PACKAGING MEETS GS-14-920 LEAD FREE
LABELLING SPECIFICATION.

CONFIDENTIAL

FCJ	title	AirMax COVER		dwg no	10058685	Rev.	B
	catalog no	-		CUSTOMER	sheet 2 of 2		