

Important Note

This product is not available in the European Union. If you live in one of these countries, please contact us for further assistance.

Power Extension Cord, Locking C19 to C20 - Heavy-Duty, 20A, 100-250V, 12 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P036-L10



C20 to C19 cord powers a server, router, switch, blade server enclosure or other network device that requires a heavy-gauge cable.

Features

C20 to C19 Power Cable for Network Devices That Require a Heavy-Gauge ConnectionThis rugged cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a server, router, switch, blade server enclosure or other network device to a UPS system or PDU. It is also an ideal replacement or upgrade from the standard power cord provided by the device's manufacturer. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Locking C19 Connector Helps Prevent Accidental Disconnection and Expensive DowntimeHaving a cable come loose accidentally can mean the loss of power and costly downtime. The locking C19 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Lifetime WarrantyThe P036-L10 is backed by a lifetime warranty, ensuring reliability and performance.

Specifications

OVERVIEW	
UPC Code	037332218322
Device Compatibility	Server; Router; Network Switch; UPS; PDU

Highlights

- Recommended for powering network devices that require heavy-gauge cabling
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Reliable replacement or upgrade from standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking C19 connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect devices like servers, routers and network switches to a UPS system up to 10-ft. (3.05 m) away in your data center
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P036-L10 C20 to C19 Power Cable, Locking C19 Connector, 10-ft. (3.05 m), Black

Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	10.8mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm ²)	3.31
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.80 x 8.59 x 0.50
Shipping Dimensions (hwd / cm)	32.51 x 21.82 x 1.27
Shipping Weight (lbs.)	1.51
Shipping Weight (kg)	0.68
ENVIRONMENTAL	
Operating Temperature Range	-4° to 221°F (-20° to 105°C)
Storage Temperature Range	-4° to 221°F (-20° to 105°C)
Operating Humidity Range	0% to 65% RH
Storage Humidity Range	0% to 65% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C19 - LOCKING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes



1000 Eaton Boulevard
Cleveland, OH 44122
United States

Locking Plug	Yes
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.