







Applications	 Commercial Grade
Feature	 No Directivity
	 Wire Wound
	 Ferrite Core
Series   Type	NLV32-EF
Status	 Production
Brand	TDK









Size	
Length(L)	3.20mm ±0.20mm
Width(W)	2.50mm ±0.20mm
Thickness   Height	2.20mm ±0.20mm
Recommended Land Pattern (A)	1.20mm Nom.
Recommended Land Pattern (B)	2.00mm Nom.
Recommended Land Pattern (C)	2.00mm Nom.

Electrical Characteristics	
Inductance	68μH ±5% at 2.52MHz
Rated Current	50mA
DC Resistance [Typ.]	
DC Resistance [Max.]	9Ω
Self Resonant Frequency [Min.]	12MHz
Self Resonant Frequency [Typ.]	
Q [Min.]	30 at 2.52MHz
Q [Typ.]	

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 105°C
Soldering Method	Wave (Flow)
	Reflow
	Iron Soldering
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [180mm Reel]
Package Quantity	2000pcs
Weight	0.05g

## Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



# Associated Images

