



PART FINDER

FIND NOW

Find faster what you're looking for!

Product Overview

Connectors

Customer specific solutions

D SUB

D SUB accessories

D SUB cover

DVI

Centronics

IDC

Modular

USB

USB 3.0 + USB 3.1

IEEE 1394

Power supply

DIN 41612

DIN 41617

Mini DIN

IC Socket

Pin and female header

LED connectors

Jumper

Connector sleeves

Solder terminals

Test terminals

Terminal Blocks

Memory Card connectors

FFC / FPC connectors

Micro-Miniature

Keystone Jack

Gender Changer

Modular Plug

Waterproof parts

Thermal management

Cable assembly

Capabilities

IT Network Products



download
technical drawing



download
Product Change Notification



3D view

D SUB

A-DS 09 A/KG-T1

D SUB

male THT 09pins euro standard
right angle

Part number: A-DS 09 A/KG-T1

product group: D SUB

style: male

contact type: THT

pin count: 9

current rating: 3A

version: euro standard

contact length: 3,20mm

contact direction: right angle

plating: Au

fastening: with locking bolts UNC

packaging: tray

process: THT

insulator: PBT, UL94V-0



USB 3.1 Cable Assemblies with PD-funktion

Download the Newsletters



MORE NEWS 



Company Film

Watch our company video!

[START WATCHING](#)

Contact

1840 W. Drake Drive, Suite 101
Tempe AZ, A
+1 (480) 8977 001
info@assmann-wsw-usa.com

[TO CONTACT](#)



 PART FINDER

 IMPRINT

 SITEMAP

 TERMS & CONDITIONS

 PRIVACY POLICY

 PRINT

 RECOMMEND