USB 2.0 A to Micro-B Cable (M/M), 10 ft. (3.05 m)

MODEL NUMBER: **U050-010**



Highlights

- Next Generation USB Digital Device Connector
- Provides both Data and Power transfers
- USB 2.0 480Mbps Transfer rates
- Standard "A" Male to Micro-B Male

System Requirements

- Digital devices that use the USB Micro-B Female socket

Package Includes

- 10-ft. (3.05 m) USB 2.0 A-Male to Micro-B Male

Features

- USB A Male to Micro-B Male
- Available in 3-ft. (0.91 m), 6-ft. (1.83 m), and 10-ft. (3.05 m) lengths
- 480Mbps USB 2.0 Data Transfer Rates
- Data and Power transference

Specifications

OVERVIEW	
UPC Code	037332160508
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	MICRO-USB B (MALE)
Connector Style	Straight
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27

Downloaded from Arrow.com.

Shipping Weight (lbs.)	0.17
Shipping Weight (kg)	0.08
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.