



Part Number : [640018800](#)
Product Description : Hand Crimp Tool for
AviKrimp Fully Insulated and Insulated Quick
Disconnect Flags, 12-10 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp
Hand Tools



Documents & Resources

Tooling Specifications
[ATS-6400188HM-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for AviKrimp Fully Insulated and Insulated Quick Disconnect Flags, 12-10 AWG
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Avikrimp,N/A
Tool Type	Hand Crimp Tool
UPC	889056261234
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Applicable Parts

Description	Part Number
Avikrimp Quick Disconnect, Female Flag, for 12-10 AWG Wire, Tab 6.35 x 0.81mm, Yellow	<u>190060019</u>
Flag InsulKrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm ²) Wire, Box, Tab 6.35 x 0.81mm	<u>190070040</u>

InsulKrimp Female Fully Insulated Quick Disconnect Flag for 12-10 AWG Wire, Tab 6.35 x 0.81mm, 94 V-0 Material	<u>190070082</u>
---	------------------

This document was generated on Mar 12, 2025