



FACT® NG4 Fiber Panel, with 4 unloaded trays, gray, 2E high, for holding 8 NG4 adapter packs or 4 NG4 MPO modules or 4 NG4 cabled LC/SC modules or 4 NG4 value added modules

- Designed for use with the all-purpose all-front-access FIST-GR3 fiber frames supporting up to 2,688 LC or 1,344 SC connections in a single frame
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber VAM panel Fiber patch panel
Product Brand	FACT®
Product Series	FACT

General Specifications

Functionality	Multiplexing Patching Splitting
Application	Compatible with FIST-GR3-style frames
Adapter Packs Included, quantity	0
Body Style	Symmetrical
Color	Gray
Color, front	Gray
Growth Configuration	Unloaded
Interface, front	Unloaded
Modules Included, quantity	0
Patch Cord Routing	Left sided Right sided
Patching Capacity, maximum	96
Rack Type	EIA 19 in
Rack Units	1.4


760239976 | FACT-2ENG4

Shelf Movement	Sliding
Splicing Capacity, maximum	0
Total Ports, quantity	0
Transmission Standards	ETSI EN 300 019-1-3 IEC 61300-3-30

Dimensions

Height	61.9 mm 2.437 in
Width	524 mm 20.63 in
Depth	283 mm 11.142 in

Ordering Tree



Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-20 °C to +85 °C (-4 °F to +176 °F)
Flammability Rating	UL 94 V-0

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

760239976 | FACT-2ENG4

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

