

Search within category

GO

BUY NOW

DESIGN / INSTALL



NC1.5WH6

Type NC halogen-free wiring duct cover, 1.5 W x 6' length, halogen-free, white.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Material	Halogen-Free PPO			
Color	White			
Type	Cover			
Length (ft.)	6.00			
Length (m)	1.8			
Cover Width (In.)	1.75			
Cover Width (mm)	44.5			
CE Compliant	Yes			
UL Recognized (File No. E147128)	Yes			
UL recognized continuous use temp	203°F (95°C)			
Flammability Rating	UL94V-0			
For Duct Width (In.)	1.50			
Height (In.)	0.35			
Part Features	Halogen-Free Cover with non-slip liner to prevent cover slide. Designed for easy install and removal.			
Width (In.)	1.75			
Width (mm)	41.7			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	6			