

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


1062250045

Status:

Active

Description:

MPO Female-to-MPO Female Trunk Cable Assembly, 9/125µm, 3.80mm, Singlemode, 12 Fiber, Plenum, OS2, 10.0m Length, Yellow



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Datasheet (PDF)	

General	
Product Family	Fiber Optic Assemblies
Series	106225
Boot Type	Straight
Connector to Connector	MPO-to-MPO
Mode	Singlemode
Product Name	MPO
Taxonomy	Fiber Optic Cable Assemblies
UPC	191128250566
Physical	
Cable Length	10.0m
Cable Size	3.80mm
Fiber (Core/Cladding)	9/125µm
Net Weight	175.073/g
Single Ended	No
Wire/Cable Type	12 Fiber OS2 Plenum
Material Info	
Reference - Drawing Numbers	
Sales Drawing	1062250037-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

106225 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION