

Search...



My account



*

Home

Medical Power Supplies

Power Supplies Industrial/ITE

Medical Charging Technology

Charging Technology Inc >

< Overview

Power Supplies Industrial/ITE >

Interchangeable Plug Power Supplies



Description

Accessories

32

Required Accessories

For the operation of this device you need a primary adapter and a secondary adapter . This can be found here:

[Primary adapters](#) and [Secondary adapters](#)

Product information "FOX30-X"

Merkmale FOX30-X: Übertrifft die Anforderungen gemäß DOE 2016, hoher Wirkungsgrad, minimale Standby-Verlustleistung $\leq 0,1$ Watt, weltweiter Einsatz durch austauschbare Primärleitung, doppelte Sicherheit: Geschnappt und verschweisst.


Additional information

- **color:** black
- **Standard:** IEC60950-1
- **Input voltage:** 100-240 V
- **Output voltage:** 7.5
- **Current:** 4000 mA
- **Country version:** FRIWO interchangeable mains plug system: see Primary Adapters
- **FW-Type:** FW8030/8
- **Protection Class:** II
- **Input tolerance:** $\pm 10\%$
- **DC output:** Universal output plug system
- **MTBF:** 200.000h acc. Mil217F (based on calculations at 120Vac/60Hz & 230Vac/50Hz, ambient 25°C and 100% load) (The MTBF are theoretically determined values, which does not guarantee the lifetime of the product or of the electrolytic)

: -40°C - 70°C

- **Working temperature:** 0°C - 45°C
- **Humidity:** 10% bis 95%
- **AC Input:** FRIWO interchangeable mains plug system: see Primary Adapters
- **Frequency:** 50 / 60
- **Output voltage tolerance:** ±5%
- **Gehäuse / Housing:** FOX30
- **Input current:** 600-300 mA
- **leakage current:** ≤10 µA
- **Overload protection:** Yes
- **Over Voltage Protection:** Yes
- **Short Ciruit protection:** Yes
- **Operating Altitude:** 2.000
- **EMV/ EMC:** EN55022, EMV55024 V
- **MTBF:** 200.000h acc. Mil217F (based on calculations at 120Vac/60Hz & 230Vac/50Hz, ambient 25°C and 100% load) (The MTBF are theoretically determined values, which does not guarantee the lifetime of the product or of the electrolytic) h
- **Dimension:** 90x55x34
- **AC Input:** FRIWO interchangeable mains plug system: see Primary Adapters
- **material:** PC-ABS
- **Length:** 1830 mm

Dokumente

Document	Action
Manual FOX30	
Flyer FOX30-X	

Similar products

Customers also bought

Customers also viewed



GPP30

5V / 5000mA worldwide



FOX6-X

5V / 1400mA worldwide



MPP30

5V / 5000mA worldwide

Service hotline

Telephone assistance and advice at:

+49 2532 81-0

Mo-Fr, 9:00am - 5:00pm

Shop service

- Contact
- General Terms and Conditions
- Payment / Dispatch
- Return
- Defective product

Information

- About us
- Data protection statement
- Imprint
- Newsletter
- Site Map

Newsletter

Subscribe to the free Firwo newsletter and ensure that you will no longer miss any of our Friwo Onlineshop offers or news.

Zur Anmeldung

* All prices are quoted net of the statutory value-added tax and [shipping costs](#) and possibly delivery charges, if not otherwise described

We use cookies to ensure to give you the best experience for you on our website. If you continue to use our website we assume that you are ok and willing to receive cookies. You can find more information about our cookies in our [data policy here](#)

Continue