



Part Number : [1301470012](#)
Product Description : Watertite Extreme Plug, 3 Pole/3 Wire, Non-NEMA, 250V, Cord Grip Body Size F3
Series Number : 130147
Status : Active
Product Category : Wiring Devices
Engineering Number : 26W08



Documents & Resources

Drawings

[1301470012_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	Not saleable
EU ELV	Not saleable
Low-Halogen Status	Not saleable
REACH SVHC	Not saleable
EU RoHS	Not saleable

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Plug, 3 Pole/3 Wire, Non-NEMA, 250V, Cord Grip Body Size F3
IP Rating	IP67
NEMA Configuration	Non-NEMA
Product Name	Watertite Extreme
Specialty	N/A
Type	Plug
UPC	78678871290

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F3 3/4"
Cord Type	N/A
Flange	No
Flip Lid	No

Gender	Male
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	1.000/g
Poles	3-pole/3-wire
Receptacle Type	N/A

This document was generated on Sep 10, 2025