
60804-1 Product Details



Active

Printed Circuit Board Disconnects

.058 DIA RECPT AU/NI/PHBZ

60804-1

TE Internal Number: 60804-1

Product Highlights View All

- Contact Type = Socket
- A Body Shape
- Disconnect Diameter = 1.47 mm
- Wire Range = 0.12-0.40² [26-22] mm [AWG]
- With Insulation Support

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

[+] Feedback

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Insulation Support	Yes

Dimensions

Insulation Diameter (mm [in])	0.89-1.65 [.035-.065]

Body Features

Body Shape	A
Disconnect Diameter (mm [in])	1.47 [0.058]
Wire Range (mm [AWG])	0.12-0.40² [26-22]
Material	Phosphor Bronze
Plating Material	Gold
Stock Thickness (mm [in])	0.25 [0.010]

Contact Features

Contact Type	Socket

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Packaging Features

Packaging Method	Reel

Other

Brand	AMP

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling



© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

Downloaded from Arrow.com.