

2000

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.


BY -

COPYRIGHT 2000

©

## REVISIONS



| P | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
|   | A9  | ECR-10-007735             | 01SEP2010 | RK  | SRE  |
|   | A10 | REVISED PER ECR-17-014011 | 17JAN2018 | SRG | MKO  |
|   |     |                           |           |     |      |
|   |     |                           |           |     |      |



## NOTES

1 MATERIAL AND COLOR: SEE TABLE

FOR PN 0-7



SCALE 1:2

|          |       |       |         |    |    |    |                                                                  |
|----------|-------|-------|---------|----|----|----|------------------------------------------------------------------|
|          | 10    | HA 10 | 1-0     | 57 | 70 | 81 | NBR 60-70 SHORE,1mm THICK<br>COLOR BLACK,ONE SIDE ADHESIVE       |
|          | 9     | HA 16 | 0-9     | 74 | 86 | 96 | EPDM 69,CONDUCTIVE<br>COLOR BLACK                                |
|          | 8     | HA 10 | 0-8     | 57 | 70 | 81 |                                                                  |
|          | 7     | HA 10 | 0-7     | 57 | 70 | 81 | NBR 60-70° SHORE,1mm THICK<br>COLOR BLACK,BOTH SIDES PLAIN       |
|          | 6     | HA 16 | 0-6     | 74 | 86 | 96 | FKM 70° SHORE (VITON),-30°C TO +200°C<br>3mm THICK,COLOR BLACK   |
| OBSOLETE | 5     | HA 10 | 0-5     | 57 | 70 | 81 |                                                                  |
|          | 4     | HA 16 | 0-4     | 74 | 86 | 96 | NBR 60-70 SHORE,1mm THICK<br>COLOR BLACK,BOTH SIDES PLAIN        |
|          | 3     | HA 10 | 0-3     | 57 | 70 | 81 |                                                                  |
|          | 2     | HA 16 | 0-2     | 74 | 86 | 96 | ZELLKAUTS CHUCK "B",ONE SIDE ADHESIVE<br>2.5mm THICK,COLOR BLACK |
| OBSOLETE | 1     | HA 10 | 0-1     | 57 | 70 | 81 |                                                                  |
|          | SI NO | TYPE  | PART NO | A  | B  | C  | MATERIAL 1                                                       |

DIMENSIONS:

mm

DWN

SCHNEIDER

05.06.2001

MATERIAL



FINISH

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC  
1 PLC  
2 PLC  
3 PLC  
4 PLC  
ANGLES

n.ISO 8015:  
n.ISO 2768-mH-E:  
n.DIN 16901-120

±



CHK

SCHWEIGER

05.06.2001

APVD

T.SCHNURPFEIL

05.06.2001

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

NAME

FLANGE MOUNTED SEAL  
SERIES HA 10/16

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A 4

00779

C-1106350

CUSTOMER DRAWING

SCALE

1:1

SHEET

1 OF 1

REV

A10