

Pushbutton, 18.2 mm, screw terminal, momentary contact function,
1 NC + 1 NO, bezel green



Description

Pushbutton with mounting hole diameter 18.2 mm, non-illuminated, 250 V / 4 A



technical data

| | | |
|--|---------------------------------------|-----------------|
| > general | | direct links |
| Bezel color | green | > RAFI eCatalog |
| Property of bezel / mushroom | opaque | |
| Collar shape | round | |
| Operating temperature, min. | -25 °C | |
| Operating temperature, max. | 85 °C | |
| Storage temperature, min. | -40 °C | |
| Storage temperature, max. | 90 °C | |
| illuminated | No | |
| Packaging | Box | |
| Packaging unit | 100 pcs. | |
| net weight | 16 g | |
| Operating life | 50,000 cycles | |
| B10 | 65,000 cycles | |
| Degree of protection, front side, according to DIN EN 60529 | IP40 IP65 IP65 with sealing cap | |
| Minimum order quantity (MOQ) | 100 pcs. | |
| RoHS compliant | Yes | |
| REACH compliant | Yes | |
| country of origin | HU | |
| > mounting diameters | | |
| Outside dimension, length | 22 mm | |
| Outside dimension, width | 22 mm | |
| Outside dimension, height | 44.5 mm | |
| Mounting hole | 18.2 mm | |
| Mounting depth | 34 mm | |
| Installation height | 10.5 mm | |
| > mechanical data | | |
| Actuation function | momentary contact function | |
| Operating force, min. | 9.5 N | |
| Operating travel, max. | 5 mm | |

| | |
|--------------------------|------------------------|
| Contact function | 1 NC + 1 NO |
| Contact system | Bridge-sliding contact |
| Contact material | Silver |
| Fixing | Threaded ring |
| Terminal on the rear | Screw terminal |
| > electrical data | |
| Rated voltage, max. | 250 V |
| Rated current, max. | 2 A |