

Color: ■ yellow Similar to illustration

Technical data	
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	3,000 labels/reel; 2 lines
Printing device	Smart Printer (thermal transfer printer)

Physical data	
Depth	0.06 mm
Marking surface	6 x 15 mm

Mechanical data	
Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data	
Color	yellow
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent
Halogen-free	Yes
Weight	99.4 g
Fire load	0 MJ





Environmental requirements	
Ambient temperature (storage)	+10 ... +21 °C
Ambient temperature (operation)	-40 ... +150 °C
Relative humidity	40 ... 50 %

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821632672
Customs tariff number	39199080888

Product classification	
UNSPSC	55121612
eCl@ss 10.0	27-40-06-29
eCl@ss 9.0	27-40-06-29
ETIM 9.0	EC001288
ETIM 8.0	EC001288
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 210-805/000-002	

Documentation	
Operating Instructions	
210-805 Information on handling print material	<div><div>1</div><div>28.08.2020</div><div>pdf</div><div>1338.18 KB</div><div></div></div>