



**Catalog No. 18RA-47PT**

**Description: INS VINYL PIN TERMINAL 22-18 RED**

**UPC No 786210034157**

**Home > Connectivity & Grounding > Sta-Kon > Electrical terminals**

Vinyl-Insulated Pin Terminal, Length .85 Inches, Pin Length .390 Inches, Diameter .075 Inches, Wire Range #22-#18 AWG, Color Red, Copper, Tin Plated

**Descriptors**

Category	Electrical terminals
Special Features	Provides an easy and effective way to terminate stranded wire into European/metric-style terminal blocks.

**Specifications**

Voltage Rating	300 V
Material	Copper
Color	Red

**Classifications**

Brand Name	Sta-Kon
------------	---------

**Dimensions**

Wire Size	22-18 AWG
-----------	-----------

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Pin shape
Insulation	Polyvinyl chloride (PVC)
Colour insulation	Red
Reel packaging	N
AWG-range	22-18
Material	Copper
Surface protection	Tinned

**by ABB**

