

- ENCLOSURE HARDWARE
- LED INDICATORS
- LIGHT PIPE SELECTOR
- LED MOUNTS, HOLDERS
- LEDs
- LIGHT PIPES
- BOARD MOUNT LED ASSEMBLIES
- PANEL MOUNT LED ASSEMBLIES
- LED LIGHTING
- SOLUTIONS
- RESOURCES

FLPOR3.28-SG



Flexible Light Pipe Assembly, 1mm. Fiber Optic Core, Right Angle, 3.2 X 6.3mm. Oval Lens, 3.28in. Length, 3mm LED, Super Green

Datasheet

3D Model

Request Samples

RoHS Docs

FEATURES	VALUE ADDED	CHECK STOCK
- Wavelength: 568nm, Typical Intensity: 120mcd, Color: Green - Assembly Includes Flexible Light Pipe, Right Angle Through-Hole Adaptor and LED - Oval Lens Cap 3.2 X 6.3mm. - Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info - Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear - Front Panel Mount Lens		