Specifications



Photo is representative





Eaton FP1308R3-R32-R

Eaton FP1308R inductor, 0.32 uH, 68 A Irms, 52 A ISAT, 0.216 mΩ resistance, SMT mounting, Ferrite, 2-pins, 400 qty.

General specifications	
PRODUCT NAME	Eaton FP1308R inductor
CATALOG NUMBER	FP1308R3-R32-R
UPC	051712234665
PRODUCT LENGTH/DEPTH	13.7 mm
PRODUCT HEIGHT	8 mm
PRODUCT WIDTH	12.95 mm
PRODUCT WEIGHT	5.89 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	68 A
ISAT	52 A
PACKAGE QUANTITY	400
MATERIAL	Ferrite
FREQUENCY RATING	Up to 2 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.216 mΩ
SERIES	FP1308R

Resources

SPECIFICATIONS AND DATASHEETS	Eaton FP1308R high current power inductors data sheet Eaton Specification Sheet - FP1308R3-R32-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.