

## SUPDMB568HW - UPS Accessory - Hardwire PDU Module

MODEL NUMBER: **SUPDMB568HW**



### Description

The SUPDMB568HW hardwire input/output PDU module converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU5000RT4U, SU6000RT4U, and SU8000RT4U) to a totally hardwired solution. Easy quick-connect terminal block allows installation of hardwire distribution module in minutes. Can accept input voltages of 120/208 or 120/240 VAC split-phase power. Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections.

### Features

- Converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU5000RT4U, SU6000RT4U, and SU8000RT4U) to a totally hardwired solution
- Easy quick-connect terminal block allows installation of hardwire distribution module in minutes
- Can accept input voltages of 120/208 or 120/240 VAC split-phase power
- Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections

## Specifications

| OVERVIEW                |              |
|-------------------------|--------------|
| UPC Code                | 037332144072 |
| OUTPUT                  |              |
| Frequency Compatibility | 50 / 60 Hz   |

### Highlights

- Converts compatible SmartOnline Hot-Swappable Modular UPS systems to hardwire input and output
- For use with input voltages of 120/208 or 120/240 VAC split-phase power
- Convenient quick-disconnect terminal block allows installation in minutes
- Manual bypass switch eliminates equipment downtime

### System Requirements

- Use with SU5000RT4U, SU6000RT4U, and SU8000RT4U split-phase SmartOnline Hot-Swappable Modular UPS Systems

### Package Includes

- SUPDMB568HW hardwire PDU
- Mounting Hardware
- Owner's Manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                                                      |
|-------------------------------------|------------------------------------------------------|
| Output Receptacles                  | Hardwire                                             |
| Output Nominal Voltage              | 120/208, 120/240                                     |
| <b>INPUT</b>                        |                                                      |
| Nominal Input Voltage(s) Supported  | 100V AC; 110V AC; 115V AC; 120V AC; 127V AC; 140V AC |
| Input Connection Type               | Split-phase hardwire (4-wire)                        |
| Voltage Compatibility (VAC)         | 100-140                                              |
| <b>PHYSICAL</b>                     |                                                      |
| Material of Construction            | Steel                                                |
| Shipping Dimensions (hwd / cm)      | 22.61 x 23.88 x 49.53                                |
| Shipping Dimensions (hwd / in.)     | 8.90 x 9.40 x 19.50                                  |
| Shipping Weight (kg)                | 3.99                                                 |
| Shipping Weight (lbs.)              | 8.80                                                 |
| Unit Dimensions (hwd / cm)          | 15.24 x 44.45 x 17.1                                 |
| Unit Dimensions (hwd / in.)         | 6 x 17.5 x 6.75                                      |
| Unit Weight (kg)                    | 5.31                                                 |
| Unit Weight (lbs.)                  | 11.7                                                 |
| <b>CERTIFICATIONS</b>               |                                                      |
| Certifications                      | Tested to UL1778 (USA), CSA (Canada), RoHS compliant |
| <b>WARRANTY</b>                     |                                                      |
| Product Warranty Period (Worldwide) | 2-year limited warranty                              |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>