



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com

GO



Search within category

GO

BUY NOW

DESIGN / INSTALL



STP28X0.2MYL

Category 6A Performance, 28AWG, F/UTP Patch Cord, CM/LSZH, Yellow, 0.2m.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Conductor Gauge (AWG)	28
Performance Level	Category 6A
Connector 2 Type	RJ45 8(8)
Connector 1 Type	RJ45 8(8)
Overall Length (ft.)	0.66
Overall Length (m)	0.2
Maximum Operating Temperature (°C)	75
Maximum Operating Temperature (°F)	167
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Maximum Storage Temperature (°C)	70
Maximum Storage Temperature (°F)	158
Minimum Storage Temperature (°C)	-40
Minimum Storage Temperature (°F)	-40
Flammability Rating	CM, LSZH-1 (60332-1)
Standards Met	IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.
Cable Color	Yellow
Length (ft.)	0.66
Termination End 1	Modular Plug
Termination End 2	Modular Plug
CE Compliant	Yes
Nominal Cable Outside Diameter (In.)	0.19
Nominal Cable Outside Diameter (mm)	4.7
UL5A Listed	No
Application	Shielded
Cable Length (ft.)	0.7
Cable Length (m)	0.2

Cable Type	F/UTP
Conductor Material	Copper
Maximum Installation Temperature (°C)	70
Maximum Installation Temperature (°F)	158
Minimum Installation Temperature (°C)	70
Minimum Installation Temperature (°F)	-40
RoHS Compliancy Status	Compliant
Min. Order Qty.	1

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)