Part Number : 2004531002
Product Description : Mini-Fit Sigma Receptacle Housing, 4.20mm Pitch, Single Row, Glow-Wire Capable, 2 Circuits
Series Number : 200453
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

2004531002_sd.pdf

2004531000-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2131370000-AS-000.pdf

2029880002-PS-000.pdf

2131370000-PS-000.pdf

1727180003-TS-000.pdf

2131370001-TS-000.pdf

2131370002-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	200453
Description	Mini-Fit Sigma Receptacle Housing, 4.20mm Pitch, Single Row, Glow-Wire Capable, 2 Circuits
Application	Wire-to-Board, Wire-to-Wire
Component Type	Receptacle
Product Name	Mini-Fit Sigma
UPC	193264048298

Agency

UL	E29179

Physical

Circuits (maximum)	2
Color - Resin	Black

Downloaded from Arrow.com.

Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.930/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Plug Housings	5559
Mini-Fit TPA2 and Mini-Fit Sigma Single Row Plug Housings	200471
Mini-Fit TPA2 and Mini-Fit Sigma Single Row Plug Housings	200488
Mini-Fit Jr. Vertical Single Row Headers	172647
Mini-Fit Jr. Right-Angle Single Row Headers	172648
Mini-Fit Jr. Right-Angle Headers	5569
Mini-Fit Jr. Vertical Headers	5566

Use with Part(s)

Description	Part Number
Mini-Fit Sigma Terminal Position Assurance (TPA) Retainer,	1727092002

Downloaded from Arrow.com.

4.20mm Pitch, UL 94V-0, Glow-Wire Capable, 2 Circuits, Natural	
Mini-Fit TPA2/Sigma Female Crimp Terminals	172718
Mini-Fit TPA2/Sigma Female Crimp Terminals	202988
Pre-Crimped Lead Mini-Fit Sigma/ TPA2 Female-to-Mini-Fit Sigma/ TPA2 Female	219670
Pre-Crimped Lead Mini-Fit Sigma/ TPA2 Female-to-Pigtail	219671
Mini-Fit TPA2/Sigma Female Low Mating Force Crimp Terminals	221442

Downloaded from Arrow.com.