



Pushing Performance
Since 1945

har-stop



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 453 1500
Specification	har-stop
HARTING eCatalogue	https://b2b.harting.com/09454531500

Identification

Category	Operator interfaces
Series	har-stop
Element	Emergency stop buttons
Specification	foolproof

Version

Diameter of the mounting hole	22.3 mm
Details	This item requires additional contact blocks and a module holder to be functional. Please select these under “Matching Products”.

Technical characteristics

Actuation path	6 mm
Tightening torque	1.5 ... 2.2 Nm Fixing nut
Operating temperature	-30 ... +70 °C
Storage temperature	-50 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67 IP69K
Thickness of the panel	1 ... 7 mm

Specifications and approvals

Specifications	EN 60947-5-1 EN 60947-5-5 EN ISO 13850
----------------	--



Pushing Performance
Since 1945

Specifications and approvals

UL / CSA	UL 60947-5-1 NISD2.E534797
	CSA C22.2 No. 60947-1:22 NISD8.E534797
	UL 60947-1 NISD2.E534797

Commercial data

Packaging size	10
Net weight	30.24 g
Country of origin	Germany
European customs tariff number	85365080
GTIN	5713140449503
ETIM	EC001038