

Part Number : [1201030005](#)

Product Description : PROFIBUS Attachable D-Sub Connector without Diagnostics LEDs, 90° Angle

Series Number : 120103

Status : Active

Product Category : Circular Industrial Connectors

Engineering Part Number : PA9S01-42


Documents and Resources

Drawings

[1201030005_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[UKCA - Declaration of Conformity](#)

[CE - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120103
Description	PROFIBUS Attachable D-Sub Connector without Diagnostics LEDs, 90° Angle
IP Rating	IP67
Product Name	D-Sub,PROFIBUS
Type	Field Attachable Connector
UPC	78678854818

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Zinc Die-Cast
Material - Contact	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Orientation	90° Angle
Poles	N/A

Temperature Range - Operating	-20° to +80°C
Wire Size (AWG)	N/A

This document was generated on Apr 29, 2026