










NOTE:
 MATERIAL:
 HOUSING: PBT+30%G.F. UL 94V-0
 CONTACT 5P: BRASS
 CONTACT 4P: PHOSPHOR BRONZE
 SHELL: BRASS
 PLATING:
 CONTACT: GOLD FLASH AND TIN OVER NICKEL PLATED
 SHELL: NICKEL PLATED OVER ALL
 SPECIFICATION:
 CURRENT RATING: 1.8A FOR VBUS AND GND CONTACTS
 1.5A FOR OTHER CONTACTS
 WITHSTANDING VOLTAGE: 100V AC(RMS)
 INSULATION RESISTANCE: 100MΩ MIN AT 100V DC
 CONTACT RESISTANCE: 30mΩ MAX FOR VBUS AND GND CONTACTS
 50mΩ MAX FOR OTHER CONTACTS
 MATING FORCE: 3.57KgF MAX
 UNMATING FORCE: 1.02KgF MIN



11/10/27	VICKY		NEW-DGW			AO	
DATE	DR.BY	ECN.NO.	DESCRIPTION			MARK	VER.
-TOLERANCES- UNLESS OTHERWISE SPECIFIED		CnC Tech,LLC					
				TITLE: USB 9P A/F DIP 90 15U" RoHS 蓝色成品			
X.X ±0.25	X.X° ±3.0°	APPD:		PRODUCT NO: 1003-001-01000			
X.XX ±0.15	X.XX° ±1.00°	CHECK:		DATE	SCALE	UNIT	PAGE
X.XXX ±0.05	X.XXX° ±0.500°	DRAW:		2011.10.27	FREE	MM	CD 1