

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A

A DIVISION OF HONEYWELL INC.

FED. MFG. CODE 91929

CATALOG LISTING

BA-2RV312T**ABS3580****SWITCH-BASIC****M** BA-2RV312T

PAGE 1 OF 1

REPLACES X87687-BA

RELEASE NO. PR-16747

DRAWING
NUMBER

5

ISSUE

REVISIONS

A	CO-89351-D	18 JUL 91
B	CO-77590	9 SEP 94
C	CO93346	DLT 26 AUG 98
D	0018387	TSG 18 JAN 06

CHECK

CHECK

18 JAN 06

RJ


CHECK

J A P 120 SEPT 88

FORMTEK

FC-52848-B

DRAWN


6-32 UNC X .218 REF BINDER
HEAD TERMINAL SCREW AND
LOCKWASHER (SEMS) (3)

NOTES

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF
.139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ——— 1 OZ MAX

RELEASE FORCE ——— 1/4 OZ MIN

DIFFERENTIAL TRAVEL ——— .234 MAX

OVERTRAVEL ——— .297 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L23 20A 125, 250, OR 480 VAC
10A 125 VAC "L"
1 HP 125 VAC, 2 HP 250 VAC
1/2 A 125 VDC, 1/4 A 250 VDC

L288
L308
L315



20(3)A 250V ~ T85 5E4

SCALE FULL

DO NOT
SCALE PRINTUNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT