

Search by part # or keyword 

Products

Industries &
Solutions

Resources

Shop TE

Sign In

[Connectors](#) > [PCB Connectors](#) > [Backplane Connectors](#) > [Eurocard Connectors](#)

5535071-4

Eurocard Connectors, Receptacle, Board-to-Board, Termination Post & Tail Length 4.57 mm [.18 in], 48 Position, 2.54mm [.1in] Centerline



EUROCARD

TE Internal #: **5535071-4**

TE Internal Description:

ASSY,RECEPTACLE,EUROCARD,TYPEConnector & Housing Type : **Receptacle**Connector System : **Board-to-Board**Termination Post & Tail Length : **4.57 mm [.18 in]**Number of Positions : **48**Centerline (Pitch) : **2.54 mm [.1 in]** [Digital Datasheet](#)**Compatible Parts & Tooling****We are here to help!**

Get in touch with our product experts.

**CHAT WITH US****EMAIL US****CALL US**

Feedback

Documents

Features

Product Compliance

Product Drawings

ASSY,RECEPTACLE,EUROCARD,TYPE

 [ASSY,RECEPTACLE,EUROCARD,TYPE](#)

English

CAD Files

PCB Design

[Download symbol & footprint \(SnapEDA\)](#)

3D PDF

 [3D_CVM_CVM_5535071-4_O.pdf](#)

3D

Customer View Model

 [ENG_CVM_CVM_5535071-4_O.2d_dxf.zip](#)

English

 [ENG_CVM_CVM_5535071-4_O.3d_igs.zip](#)

English

 [ENG_CVM_CVM_5535071-4_O.3d_stp.zip](#)

English

Product Specifications

Application Specification

 [ENG_SS_114-9014_K.pdf](#)

English

Product

MD_5535071-4_07212016456_dmttec

Environmental Compliance	ENG_PC_MD_5535071-4_C(439362).xlsx English MD_5535071-4_07212016456_dmtec ENG_PC_MD_5535071-4_C(874365).xml English
Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.	
Product Type Features	Connector & Housing Type : Receptacle Connector System : Board-to-Board Sealable : No Connector & Contact Terminates To : Printed Circuit Board DIN Size : Half DIN Level : II
Configuration Features	Number of Positions : 48 Number of Rows : 3 PCB Mount Orientation : Vertical Number of Columns : 16 Rows Loaded : A, B, C Number of Signal Positions : 48
Termination Features	Termination Post & Tail Length : 4.57 mm [.18 in]
Mechanical Attachment	Connector Mounting Type : Board Mount
Housing Features	Centerline (Pitch) : 2.54 mm [.1 in]
Dimensions	Row-to-Row Spacing : 2.54 mm [.1 in]
Usage Conditions	Operating Temperature Range : -55 – 105 °C [-67 – 221 °F]
Operation/Application	Circuit Application : Signal
Statement of Compliance	Statement of Compliance pdf

[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)