


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191640057](#)
Status: **Active**
Overview: [Splices](#)
Description: Perma-Seal Butt Splice for 10-12 AWG Wire, Mylar Tape Carrier

Documents:
[3D Model](#) [Drawing \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Splices
Series	19164
Crimp Quality Equipment	Yes
Overview	Splices
Product Name	Butt - Funnel Entry, Perma-Seal
UPC	800753113428
Physical	
Barrel Type	Closed
Color - Resin	Yellow
Insulation	NiAc
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3.422/g
Packaging Type	Adhesive Tape on Reel
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	7.87mm max.
Wire Size AWG	10, 12
Electrical	
Voltage - Maximum	600V
Material Info	
Engineering Number	SC-12-10T



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2020)4578-DC (25 June 2020) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Contained

Search Parts in this Series
[19164](#) Series

Application Tooling FAQ <i>Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.</i> Global	
Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880279
PremiumGrade Hand Crimp Tool	640017400
Power Crimp Tool Head for Terminals 10-22 AWG Wire	640057400
ServiceGrade Hand Crimp Tool - Ratchet	640160041

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION