



CT40400SSBC0, Nylon Cable Tie, 40 lb Tensile Strength, Stainless Steel Barb, 14.49" Long, Black

By Burndy
Catalog # [CT40400SSBC0](#)

Nylon UNIRAP™ Stainless Steel Barb Cable Tie - 40 Lb. Tensile Strength



Features

- Stainless Steel Barb Tie
- Nylon 6/6, Self-locking
- Maximum strength and adjustability for versatility

Application

For use with self-locking stainless steel barb

Specifications

Buy American Compliant	No
Certification - cULus	Yes
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes

Dimensions

Dimension - Width inch	0.14 in
Package Length	18.000 in
Dimension - Width mm	3 mm
Package Width	4.250 in
Package Weight	0.430 lb.
Dimension - L Length Overall mm	368 mm
Package Height	1.300 in
Length	14.49 in

Dimension - Bundle Diameter Max inch	4.09
Dimension - Length Overall inch	14.49 in
Width	0.14 in

Force Related

Rating - Minimum Tensile Strength lbs	40 lb
---------------------------------------	-------

General

Sub Brand	UNIRAP,CABLE TIE
Series	UNIRAP™ Series
Trade Name	UNIRAP™
Color	Black
Type	CT-SSB
UPC 14 Digit GTIN	00781810564578
Material	NYLON 6/6
UPC	781810564578

Logistics

Minimum Pack Quantity	100
Carton Quantity	8000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)

