

YAEV25H

by Burndy
Catalog ID: YAEV25H

Ring Tongue Terminal, Straight, 600 V, 0.83 in W, 2.82 in L, Nylon insulation, Tin Plated, 1/0 AWG, AN 1/0, 3/8 in stud size



Product Details

General

Color Code	Blue
Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	INSULUG™
UPC	781810027394
UPC 12 Digit	7818100273944

Dimensions

Dimension - Bolt Hole Size inch	0.39 in
Dimension - D inch	0.44 in
Dimension - Length Overall inch	2.82 in
Dimension - N inch	0.42 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	11/16 in
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 1/0
--------------------------------------	--------

Conductor - Copper Str Size	1/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)