




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-	B	REVISED PER ECO-15-005333	07JUL2015	AP RP



NOTES:

- 1 MATERIAL : - HOUSING : POLYESTER G.F.
COLOUR : GREY.
- CONTACTS : PHOSPHORBRONZE.
- 2 FINISH : -1: EIC 60603-2 PERFORMANCE LEVEL I OVER NICKEL
IN CONTACT AREA.
AT POST AREA 2,5µm Sn OVER 1,25µm NI.
-4: EIC 60603-2 PERFORMANCE LEVEL II OVER NICKEL
IN CONTACT AREA.
AT POST AREA 2,5µm Sn OVER 1,25µm NI.
- 3 FOR P.C.B.-THICKNESS 1,6-2,4

P.C.B. HOLE DIM. ACTION PIN	
DRILLED HOLE	: 1,15 ± 0,025 mm
FIN. HOLE	: 0,94 to 1,09 mm
AFTER REFLOW	: 0,91 to 1,09 mm
Cu-thks	: 0,025 to 0,075 mm
SnPb-thks	: 0,004 to 0,010 mm

ROW	z b d	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2
POS		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X

AN ASTERISK „X” DENOTES A CONTACT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
0 PLC	± -		
1 PLC	± -		
2 PLC	± -		
3 PLC	± -		
4 PLC	± -		
ANGLES	± -		
MATERIAL		FINISH	

OBSOLETE	SEE NOTE 2	SEE NOTE 1	188826-4
	FINISH	MATERIAL	PARTNUMBER

DWN J.GIBBELS 180CT95		TE Connectivity	
CHK R.V.LOKVEN			
APVD -		NAME	
PRODUCT SPEC -		31 POS. TYPE F FEMALE B.T.B. - A.P. CONNECTOR.	
APPLICATION SPEC -		RESTRICTED TO	
SIZE	CAGE CODE	DRAWING NO	
		A300779	C-188826
CUSTOMER DRAWING		SCALE	SHEET
		NTS	1 OF 1
		REV	B