


REV.	DATE	ECR NO.	DESCRIPTION
NC	02/08/03	--	INITIAL RELEASE
A	09/14/10	2012	HARDWARES REMOVED



DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/112/112660.DWG	DWG. NO.	112660.DWG	REV.	A	SIZE	A	SCALE	NA
8														
7														
6	MOUNTING POST	BRASS	BRT. TIN	2										
5	POST	COPPER	BRT. TIN	2										
4	HOUSING	PBT	NATURAL	1										
3	CONTACT PIN	BER. COPPER	GOLD	2										
2	INSULATOR	POLY PRO	WHITE	1										
1	BODY	ZINC DIE CAST	NICKEL	1										
					APPROVALS		DATE		Amphenol Connex					
					DRAWN		G.R.S.		02/24/03		PART DESCRIPTION			
					CHECKED						DUAL PORT BNC R/A PCB			
					ISSUED						MOUNT RECEPTACLE - WHITE 75ohm			
					SHEET		1 OF 1				PART NO.			
											112660			

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:

0.5 - 8mm ± 0.20 mm

8 - 30mm ± 0.40 mm

30 - 120mm ± 0.50 mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:

.020 - .315 = ± 0.007 "

.315 - 1.180 = ± 0.015 "

1.180 - 4.724 = ± 0.020 "