

5

4

3

2

1

D

UNC 4-40

C


4,5

51 ±0,5

B

Screw to be used for hoods with part numbers 09 67 0XX 0425 and 09 67 0XX 0435 (XX = 09, 15 or 25 poles)

A

					Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	Knurled screw UNC 4-40 with grey knob for D-Sub hoods	Maßstab/ Scale 5:1	
			Detail.	09/10/09	PK					
			Insp.							
			Stand.							
			HARTING EURL F-95972 Paris					TB 09 67 002 9081	Blatt/ Page 1 / 1	
EC00871	19/10/09	PK								
Mod.	Dot.	Name							Sub.	

