

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 19
© COPYRIGHT 2000 ALL RIGHTS RESERVED.


LOC	DIST
J	-

REVISIONS

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
	G4	REVISED	ECR-12-001355	23JAN2012	TS	KB
	G5	REVISED	ECR-12-009464	20JUN2012	TS	KB
	G6	REVISED	ECR-16-003774	31OCT2016	KF	HY
	G7	REVISED	ECR-23-188923	15FEB2024	AG	RK







1. 嵌合相手ハウジング型番 : TABLE -1参照
2. 回路番号:FIG 1 参照
3. 端子構成 FIG 1 参照
4. 推奨取付ねじ:JIS B1115.B1122タッピングねじ、なべ2種、呼び径3、長さはTABLE-2参照
5. ねじ締付トルク(参考値):0.392N·m MAX
6. ⌖ 0.3Ⓜ Z YⓂ DTMⓂ 但し、
   3次DTMについては、S,T,W,Xを各々のブロック毎に適用すること
7. Zより7.5mmの位置で測定
8. コンタクト仕上識別記号:表参照
9. 取扱説明書 NO. :411-5932

TABLE-1

POS	PLUG HOUSING PART NUMBER
34	1123337 1674925
35	1123338 1674558
35	1123340 1674928
31	1123341 1674919

TABLE-2

プリント基板板厚(mm) THICKNESS OF PCB(mm)	1.2	1.6
固定用ねじ首下長さ(mm) NOMINAL LENGTH OF SCREW(mm)	5	6

1. PART NO OF PLUG HOUSINGS TO BE MATED : SEE TABLE -1
2. CIRCUIT NUMBERS ; SEE FIG 1
3. DETAIL OF TERMINAL SIZE; SEE FIG 1
4. RECOMMENDED SCREW: PAN-HEADED, TYPE 2 TAPPING SCREW, NOMINAL DIAMETER 3mm LENGTH:SEE TABLE-2 (JIS B1115, B1122).
5. FASTENING TORQUE FOR SCREW(REF): 0.392N·m MAX.
6. ⌖ 0.3Ⓜ Z YⓂ DTMⓂ
   TERTIRY DATUM; S,T,W,X OF EACH BLOCK.
7. MEASURED AT 7.5mm FROM Z
8. IDENTIFICATION MARK FOR THE CONTACT FINISH; SEE TABLE
9. INSTRUCTION SHEET NO.;411-5932

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 尺 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 : ± 0.3

0 PLC	±
1 PLC	±0.1
2 PLC	±0.05
3 PLC	±0.025
4 PLC	±0.000
ANGLES	±°

MATERIAL 材料: SEE TABLE CONTACT:BRASS

FINISH 仕上: SEE TABLE

DWN	Y.NOGUCHI	28AUG2000
CHK	N.SAI	28AUG2000
APVD	N.SAI	28AUG2000
PRODUCT SPEC 製品資格	108-5674	
APPLICATION SPEC 設計適用資格	114-5217,5250	
WEIGHT	SEE TABLE	

TE Connectivity

NAME 名称: 025/040 ECU CONNECTOR I35 POSITION CAP HOUSING ASSEMBLY

SIZE A1 | CAGE CODE 00779 | DRAWING NO 図番 C-1376430 | RESTRICTED 尺

CUSTOMER DRAWING | SCALE 尺度 2:1 | SHEET 1 OF 3 | REV G7

4805 (3/11)


Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 ALL RIGHTS RESERVED.

LOC	DIST
J	-


REVISIONS 改訂

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
		SEE SHEET 1 OF 3				




MARKING D

△10 FIG. 2



MARKING E

OBSOLETE	E	C	∅2.63	PAPER BOX ダンボール箱	PLASTIC TUBE プラスチックチューブ	35	-	SELECTIVE TIN (MATTE)	SELECTIVE TIN (BRIGHT) × 125 SELECTIVE GOLD × 10	-	87,88,89,95,96,97 119,120,129,130	PBT	BLACK	SPS	NATURAL	3-1376430-2
	E	C	∅2.63	PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	35	-	SELECTIVE TIN (MATTE)	SELECTIVE TIN (BRIGHT) × 125 SELECTIVE GOLD × 10	-	87,88,89,95,96,97 119,120,129,130	PBT	BLACK	SPS	NATURAL	3-1376430-1
OBSOLETE	D	15	∅2.4	PAPER BOX ダンボール箱	PLASTIC TUBE プラスチックチューブ	39	-	SELECTIVE TIN (MATTE)	SELECTIVE GOLD × 135	1 TO 7,32 TO 37 67 TO 73,102 TO 108	8 TO 31,38 TO 66 74 TO 101,109 TO 135	PBT	NATURAL	PBT	NATURAL	3-1376430-0
OBSOLETE	D	14	∅2.4	PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ		-	SELECTIVE TIN (MATTE)	SELECTIVE TIN (BRIGHT) × 125 SELECTIVE GOLD × 10	-	87,88,89,95,96,97 119,120,129,130	PBT	NATURAL	PBT	NATURAL	2-1376430-8
	D	13	∅2.4	PAPER BOX ダンボール箱	PLASTIC TUBE プラスチックチューブ		-	SELECTIVE TIN (MATTE)	SELECTIVE TIN (BRIGHT) × 125 SELECTIVE GOLD × 10	-	23,24,25,31,48,49 51,59,60,63	PBT	NATURAL	PBT	NATURAL	2-1376430-7
OBSOLETE	D	10	∅2.4	PAPER BOX ダンボール箱	PLASTIC TUBE プラスチックチューブ	39	-	SELECTIVE TIN (MATTE)	SELECTIVE TIN (BRIGHT) × 127 SELECTIVE GOLD × 8	-	23 TO 25 29 TO 31,48, 49	PBT	NATURAL	PBT	NATURAL	2-1376430-4
	E	61	∅2.4	PAPER BOX ダンボール箱	PLASTIC TUBE プラスチックチューブ		-	SELECTIVE TIN (MATTE)	SELECTIVE GOLD × 68 SELECTIVE TIN (BRIGHT) × 67	67,68	18 TO 31,48 TO 66 86 TO 101,119 TO 135	PBT	NATURAL	PBT	NATURAL	6376430-2
	E	1	∅2.4	PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ		-	SELECTIVE TIN (MATTE)	SELECTIVE GOLD × 68 SELECTIVE TIN (BRIGHT) × 67	67,68	18 TO 31,48 TO 66 86 TO 101,119 TO 135	PBT	NATURAL	PBT	NATURAL	6376430-1
	SEE DRAWING 1-1376430-7															2-1376430-2 1-1376430-7
	SEE DRAWING 2-1376430-1															2-1376430-1
	D	A	∅2.4	PAPER BOX ダンボール箱	PLASTIC TUBE プラスチックチューブ	39	-	PRE-TIN	PRE-TIN × 135	-	-	PBT	NATURAL	PBT	NATURAL	1-1376430-8
	SEE DRAWING 1-1376430-6															1-1376430-6
	D	9	∅2.4	PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	39	-	SELECTIVE TIN (MATTE)	SELECTIVE TIN (BRIGHT) × 129 SELECTIVE GOLD × 6	-	49,54,55,60,88,89	PBT	NATURAL	PBT	NATURAL	1-1376430-3
	D	6	∅2.4	PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ		-	SELECTIVE TIN (MATTE)	SELECTIVE TIN (BRIGHT) × 129 SELECTIVE GOLD × 6	-	46,48,49,59,60,65	PBT	NATURAL	PBT	NATURAL	1-1376430-2
	D	3	∅2.4	PAPER BOX ダンボール箱	PLASTIC TUBE プラスチックチューブ	SAME AS 1376430-5										1-1376430-0
OBSOLETE	D	5	∅2.4	PAPER BOX ダンボール箱	PLASTIC TUBE プラスチックチューブ	39	-	SELECTIVE TIN	PRE-TIN × 127 SELECTIVE GOLD × 8	-	23 TO 25 29 TO 31,48, 49	PBT	NATURAL	PBT	NATURAL	1376430-7
	D	4	∅2.4	PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	34	18 TO 25,48 TO 58 86 TO 93,119 TO 128	PRE-TIN X 98		-	-	PBT	NATURAL	PBT	NATURAL	1376430-6
	D	3	∅2.4	PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	39	-	PRE-TIN X 135		-	-	PBT	NATURAL	PBT	NATURAL	1376430-5
	LOCATION 位置	CHARACTER △10 文字	V	OUTER 外装	INNER 内装	WEIGHT (g)	NO CONTACT CIRCUIT NO 次番 △1	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	040TAB	025 TAB	MATERIAL 材料	COLOR 色	MATERIAL 材料	COLOR 色	PART NUMBER 製品型番
	MARKING マーキング △8			PACKING STYLE 梱包形態				CONTACT FINISH コンタクト仕上げ		GOLD PLATED CIRCUIT NO 金めっき回路番号		TINE PLATE タインプレート		HOUSING ハウジング		



△2, △3 FIG. 1

O:040 CONTACT

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN -	TE Connectivity	
DIMENSIONS: 単位: 尺 mm	CHK -	NAME 名称	025/040 ECU CONNECTOR 135 POSITION CAP HOUSING ASSEMBLY
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差: ±0.3 0 PLC ± ; 1 PLC ±0.1 ; 2 PLC ±0.05 ; 3 PLC ±0.025 ; 4 PLC ±0.0001 ; ANGLES ±3°00'	APVD -	PRODUCT SPEC 製品規格	SEE 1 OF 3
		APPLICATION SPEC 設計適用規格	SEE 1 OF 3
MATERIAL 材料 SEE TABLE	FINISH 仕上 SEE TABLE	WEIGHT SEE TABLE	SIZE A1 · CAGE CODE 00779 · DRAWING NO 1376430 · RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 1:1 · SHEET 2 OF 3 · REV G7


Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT 2000 ALL RIGHTS RESERVED.

LOC	DIST
J	-

REVISIONS 変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 OF 3			





CAP HOUSING ASSEMBLY & PLUG HOUSING ASSEMBLY ENGAGEMENT VIEW
CAP HOUSING ASSEMBLY & PLUG HOUSING ASSEMBLY 嵌合図

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 粍 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 = ±0.3

0 PLC	± -
1 PLC	±0.1
2 PLC	±0.05
3 PLC	±0.025
4 PLC	±0.0003
ANGLES	±3°

MATERIAL 材料: SEE TABLE

FINISH 仕上: SEE TABLE

DWN -
CHK -
APVD -

PRODUCT SPEC 製品規格: SEE 1 OF 3

APPLICATION SPEC 取付適用規格: SEE 1 OF 3

WEIGHT: SEE TABLE

CUSTOMER DRAWING

TE Connectivity

NAME 名称: 025/040 ECU CONNECTOR 135 POSITION CAP HOUSING ASSEMBLY

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-1376430	-

SCALE 尺度	SHEET	REV
1:1	3 OF 3	G7

Downloaded from Arrow.com.