



MT1200H200BQI780

(active)

- Input voltage: 198~440 VAC
- Output current range: 60~2000mA (programmable)
- Dimming performance: 0→5%→100% dimming range, Flicker Free, Linear/Logarithmic Curve
- Various programming methods: Smart key programming

Recommended Options

Learn More About 1200W/1800W Stadium Lighting LED Drivers

Brand Name:

MOONS'

Quantity:

-

1

+

Shipping to:

United States

▾

Lead Time:

Contact customer service

Request For Quote

Add to compare

* Free shipping to North America and most of Europe for orders of \$100 or more

Payment Methods



Collection

Consultant

Buyer Protection:

Free Exchange if the item has quality problems within 1 year. Learn more

Specification

Downloads

Recommended Options

Parameter	Unit	Value
V_in	Vac	198-440
Frequence	Hz	47~63
Efficiency (120Vac)		95%
Efficiency (230Vac)		96%
P_out	W	1200
Driver Type		CC
V_out	V	170-415
I_out	mA	60-2000
Dimming Mode		DMX-RDM,DALI-2
Dimming Range		5%-100%
Certification		ENEC,CE,CB,RCM,CCC
IP Rating		IP66
Output Channels		2
Line Regulation		1%
Operating temperature		-40 ~ +50°C
Surge Level		L-N: 10KV, L/N-FG: 10KV
Size	mm	500x141x120
Weight	kg	5.7

Recommended Options



SmartKey

\$75.00

All MOONS' Intelligent (0-10V, DALI, DMX) Drivers can be programmed through Smartkey Network Software.Such as dimming solution, output current value, minimum dimming level, dimming curve.

Filter By Product Type

- ☒ All Products
- ☐ Configurator



Email

Name

Select Your Industry ▾

SUBSCRIBE

