





PRODUCT NUMBER	PITCH
HAxx30x000J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item①Lever: Thermoplastic (UL94V-0) Orange (RAL2011/P)
- Item②Terminal body: Thermoplastic (UL94V-0)
- Item③cover: Thermoplastic (UL94V-0)
- Item④Spring clamp: Stainless steel
- Item⑤contact pin: Brass Tin plated

Electrical cULus/VDE

- Voltage rating: 300VAC/250VAC
- Current rating: 10A/10A
- Wire range: 0.75-1.5mm²
- Solid wire(AWG): 14-24
- Stranded wire(AWG): 14-24
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV/2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:

N=Number of poles
Dim L=Nx5.0+2.54
Dim P=(N-1)x5.0

POLES	Dim L	Dim P
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

PART NO.: HA xx 30 x 0 00J0 G

End stackable	No. of poles	Color	RoHS compliant
0	2	Black (RAL9005)	(lead<4%)
02	2 poles	Red (RAL3001/D)	In copper Alloy
03	3 poles	Orange(RAL2011/P)	
...	...	4 Yellow(RAL1018/A)	
...	...	5 Green(RAL6018/T)	
24	24 poles	6 Blue (RAL5015/A)	
		8 Grey(RAL7004/P)	
		9 White(RAL1102)	
		C Multiple colors	

mat'l. code				surface	tolerance	projection	product family		
ltr ecn no dr date				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK		
				tolerances unless otherwise specified		MM	title		
				angles	X.±0.5		TERMINAL BLOCK		
				holes	X.X±0.3		SPRING CLAMP, 90D WIRE INLET		
				X*±1°	X.XX±0.1	scale			
				dr	EVIN ZHONG 052314		dwg no		sheet 1 of 1 size
				enr	EVIN ZHONG 052314		HAxx30x000J0G		A4
				chr	HANKE FENG 052314				
				appd	SHI JUN 052314		type CUSTOMER Drawing		
sheet index	revision sheet	A	1						