



TLS 2200®/TLS PC Link™ Labels

TLS 2200®/TLS PC Link™ Label Index By Size (Continued)

Diagram	Catalog Number	Labels Per Roll	Material	Color	B-Number	Label Width Inch (mm) A	Label Height Inch (mm) B	Write-On Height Inch (mm) C	Wire Gauge
1.765" (Continued)									
Fig. 20	PSPT-250-175-OR	100	Polyolefin	Orange	B-342	1.765 (44.8)	0.439 (11.2)	—	—
Fig. 20	PSPT-250-175-PK	100	Polyolefin	Pink	B-342	1.765 (44.8)	0.439 (11.2)	—	—
Fig. 20	PSPT-250-175-RD	100	Polyolefin	Red	B-342	1.765 (44.8)	0.439 (11.2)	—	—
Fig. 20	PSPT-250-175-VT	100	Polyolefin	Violet	B-342	1.765 (44.8)	0.439 (11.2)	—	—
Fig. 20	PSPT-250-175-WT	100	Polyolefin	White	B-342	1.765 (44.8)	0.439 (11.2)	—	—
Fig. 20	PSPT-250-175-YL	100	Polyolefin	Yellow	B-342	1.765 (44.8)	0.439 (11.2)	—	—
Fig. 20	PSPT-375-175-WT	100	Polyolefin	White	B-342	1.765 (44.8)	0.645 (16.4)	—	12 to 6
Fig. 20	BPSPT-375-175-WT	1000	Polyolefin	White	B-342	1.765 (44.8)	0.645 (16.4)	—	12 to 6
Fig. 20	PSPT-375-175-YL	100	Polyolefin	Yellow	B-342	1.765 (44.8)	0.645 (16.4)	—	12 to 6
Fig. 20	BPSPT-375-175-WT	1,000	Polyolefin	White	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-BK	100	Polyolefin	Black	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-BL	100	Polyolefin	Blue	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-BR	100	Polyolefin	Brown	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-GR	100	Polyolefin	Green	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-GY	100	Polyolefin	Grey	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-OR	100	Polyolefin	Orange	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-PK	100	Polyolefin	Pink	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-RD	100	Polyolefin	Red	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-VT	100	Polyolefin	Violet	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-WT	100	Polyolefin	White	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-375-175-YL	100	Polyolefin	Yellow	B-342	1.765 (44.8)	0.645 (16.4)	—	—
Fig. 20	PSPT-500-175-WT	100	Polyolefin	White	B-342	1.765 (44.8)	0.851 (21.6)	—	8 to 1
Fig. 20	BPSPT-500-175-WT	1000	Polyolefin	White	B-342	1.765 (44.8)	0.851 (21.6)	—	8 to 1
Fig. 20	PSPT-500-175-YL	100	Polyolefin	Yellow	B-342	1.765 (44.8)	0.851 (21.6)	—	8 to 1
Fig. 20	BPSPT-500-175-WT	1,000	Polyolefin	White	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-BK	100	Polyolefin	Black	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-BL	100	Polyolefin	Blue	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-BR	100	Polyolefin	Brown	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-GR	100	Polyolefin	Green	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-GY	100	Polyolefin	Grey	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-OR	100	Polyolefin	Orange	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-PK	100	Polyolefin	Pink	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-RD	100	Polyolefin	Red	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-VT	100	Polyolefin	Violet	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-WT	100	Polyolefin	White	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-500-175-YL	100	Polyolefin	Yellow	B-342	1.765 (44.8)	0.851 (21.6)	—	—
Fig. 20	PSPT-1000-175-WT	50	Polyolefin	White	B-342	1.765 (44.8)	1.660 (42.2)	—	1 to 500

Figure 20

