

6

5

4

3





2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/25/14	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Screw: Steel, M3.0/Zinc plated

Cage: Brass, Nickel plated

Pin Header: Brass, Tin plated

Electrical:

Voltage rated: 300 VAC

Current rated: 16 Amps

Contact resistance: 20 mΩ

Insulation resistance: 500 MΩ @ 500 VDC

Withstanding voltage: 2000V AC/1 Min

Mechanical:

Solid wire: 26-12AWG 2.5mm²

Torque (Lb-in): 0.5Nm (4.5lb-in)

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.

Positions: 02 thru 24
 A = .197 [5.00] x No. of Positions
 B = .197 [5.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

.X ± .10 ØXX ± .10
 .XX ± .020 ØXX ± .015
 .XXX ± .015 ØXXX ± .010

APPROVALS

APPROVALS	DATE
DRAWN AY	8/25/14
CHECKED SC	8/25/14
APPROVED	

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

EURO BLOCK, .197 [5.00] PITCH

SIZE	PART NO.	REV.
X	EB147A-XX-C	-
REF: S00067C	SCALE: NTS	SHEET 1 OF 1

