
AMPHENOL PN
10197766-2030LF



WIRING LIST		
CON1		CON2
PIN1	RED	PIN1
PIN2	GRAY	PIN2
PIN3	GRAY	PIN3
PIN4	GRAY	PIN4
•		
•		
•		
PIN19	GRAY	PIN19
PIN20	GRAY	PIN20

NOTES:

1. ALL CABLE ASSEMBLIES SHALL BE TESTED 100% FOR CONTINUITY AS DEFINED IN WIRING LIST.
2. UNLESS OTHERWISE SPECIFIED ALL CABLE ASSEMBLIES SHALL BE TESTED:
   HI-POT: DC 300V/10ms.
   DIELECTRIC RESISTANCE: 10M Ohms MIN.
   CONNECTION RESISTANCE: 3 Ohms MAX.
3. LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES.

Qty	Unit	Description	Item
/	M	Flat Cable, UL2678, 30AWG*20C, PITCH: 0.635MM	2
2	EA	IDC CONN.: 1.27PITCH, 2X10PIN, 0.25um GOLD AT CONTACT, BLACK, 20021444-00020T4LF	1

mat'l. code	surface ISO 1302	tolerance ISO 406 ISO 1101	projection
	tolerances unless otherwise specified		

Cable Assembly

ltr	ecn no	dr	date
A		Jacob	3/23'26

angles | linear | MM | scale N/A

title: IDC CABLE ASSEMBLY

dr	Jacob Ding	3/23'26
engr	Jacob Ding	3/23'26
chr	TIM YAO	3/23'26
appd	TIM YAO	3/23'26

Amphenol FCi

dwg no 10197766-2030LF | sheet 1 of 1 | size A3

type: Customer / Drawing

sheet index | revision A | sheet

© 2016 AFCI

PDS: Rev :A STATUS:Released Printed: Mar 25, 2026

Downloaded from Arrow.com.