

## Catalog No. 54854BEUB

**Description:** CU 2HL LUG 90D STDBRL No6 No10B BLU

**UPC No** 786210556871

**Home > Connectivity & Grounding > Color Keyed / Blackburn > Cable or wire lug**

Copper Two-Hole Lug, 90 Degree Bend Long Barrel, Blind End, Max 35kV, Wire Size #4 AWG, 1/4 Inch Bolt Size, 5/8 Inch Hole Spacing, Tin Plated, Die Code 29, Die Color Code Gray



Representative Image

### Descriptors

Category	Cable or wire lug
----------	-------------------

### Specifications

Cable Size	4 AWG
Number Of Holes	2
Voltage Rating	35 kV
Insulation	None
Material	Copper
Color	Gray

### Classifications

Brand Name	Color Keyed / Blackburn
Standard	UL E9809

### Dimensions

Stud Size	1/4 in
-----------	--------

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	90°
Slender flange model	N
Insulated	N
With sight-hole	N

**by ABB**

ETIM	EC001051 Tube cable lug for copper conductors
Material	Copper
Surface protection	Tinned
Number of mounting holes	2
AWG size	4

**Certification/Standard**

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	N/A	N/A
UL	E9809	N/A	N/A	N/A	N/A