



Part Number : [192130008](#)
Product Description : Avikrimp Wire Pin
Terminal for 12-10 AWG Wire, Mylar Tape
Carrier
Series Number : 19213
Status : Active
Product Category : Crimp Terminals
Engineering Number : WP-8210T
Packaging Alternative : 192130007 (Bag)



Documents & Resources

Drawings
[192130008_sd.pdf](#)

3D Models and Design Files
[192130008_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	19213
Description	Avikrimp Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier
Application	Power, Wire-to-Component
Comments	Pin Length 11.68mm
Product Name	Wire Pin
UPC	800753053489

Agency

CSA	LR18689
UL	E32244

Physical

Flammability	94V-2
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	2.203/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	1.016µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	6.35mm max.
Wire Size (AWG)	10, 12
Wire Size mm ²	N/A

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880179</u>
Mini-Mac Pneumatic Applicator for Industrial Terminals 26-6 AWG	<u>638851500</u>

This document was generated on Mar 03, 2025