

Honeywell Sensing and Control

Search

3450HR 84550019

(Home : Products : Sensors » Thermostats » 3450HR)

narrow your search

Products

- Controls
 - Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (5910)
- Switches (9781)
- Wireless (45)

Technology

- Electromechanical (9307)
- Magnetic (541)
- Microstructure (1495)
- Optical/Infrared (1042)
- Thick Film (1409)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

[Click here to contact us](#)


3450HR Series Phenolic Automatic Reset Thermostats

Actual product appearance may vary.

[Sales & Service](#)
[Distributor Inventory](#)
[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	15 A/10 A resistive max.
Voltage	120 Vac/240 Vac
Operating Temperature	0 °C to 150 °C [32 °F to 302 °F]
Environmental Exposure Range	-18 °C to 177 °C [0 °F to 350 °F]
Open Temperature	65.0 °C [149 °F]
Close Temperature	56.1 °C [133 °F]
Open Tolerance	2.8 °C [5 °F]
Close Tolerance	4.4 °C [8 °F]
Housing Material	Phenolic
Contact Material	Silver/nickel alloy
Agency Approvals and Standards	UL, CSA
Mounting	B201 fixed bracket
Series Name	3450HR

contacts

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.


[Meet Dr. Larry](#)

my links

- [Login to iCOM](#)
- [Login to Rep/AD Portal](#)
- [Login to Digital University](#)

News Center

- HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION
- HONEYWELL INTRODUCES MICROPPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

MICRO SWITCH Anniversary site

