

RG59 Coax Cable with F-Type Connectors, 12 ft.
(3.66 m)

MODEL NUMBER: A200-012



Highlights

- Double Shielded RG59 Coax
- Gold Plated screw type F connectors
- Fully molded ends ensure long life use

Package Includes

RG59 Coax cable with F-Type Connectors - 12-ft. (3.66 m)

Features

- Double Shielded (Foil and Braid) RG59B/U Cable
- 24K Gold Plated screw type F connectors
- Fully molded ends ensure long life use
- Use with Cable or Satellite Receivers, VCR, DVD, Coax enabled TV

Specifications

| OVERVIEW | |
|---------------------------------|----------------------|
| UPC Code | 037332146663 |
| Technology | Coax; RG59/RG6 |
| Cable Type | Passive |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Length (ft.) | 12 |
| Cable Length (m) | 3.66 |
| Shipping Dimensions (hwd / in.) | 0.50 x 6.00 x 7.00 |
| Shipping Dimensions (hwd / cm) | 1.27 x 15.24 x 17.78 |
| Shipping Weight (lbs.) | 0.30 |



1000 Eaton Boulevard
Cleveland, OH 44122
United States

| | |
|-------------------------------------|-----------------------------|
| Shipping Weight (kg) | 0.14 |
| CONNECTIONS | |
| Side A - Connector 1 | F-TYPE (MALE) THREADED COAX |
| Side B - Connector 1 | F-TYPE (MALE) THREADED COAX |
| Latching or Gripping Connector | No |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.