

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	15[mm]
Max. Air Flow:	7[CFM]
Max. Air Flow:	0.2[m3 per min]
Max. Static Pressure:	0.188[In H2O]
Max. Static Pressure:	47.1[Pa]
Fan Speed:	7000[RPM]
Noise:	31[dB]
Life Expectancy:	25 degree C 60,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	10.2[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.075[A]
Input Power:	0.9[W]
Mass:	20[g]
Tach / Locked Rotor Output:	No
Status:	EOL