
Part Number : 368770008
Product Description : Ditto Hermaphroditic Crimp Housing, Friction Lock, 8 Circuit, Natural
Series Number : 36877
Status : Obsolete
Product Category : Connector Housings



Documents and Resources

Drawings

368770008_sd.pdf

368770008_stp.zip

Specifications

TS-36876-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Obsolete

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	36877
Description	Ditto Hermaphroditic Crimp Housing, Friction Lock, 8 Circuit, Natural
Application	Wire-to-Wire
Product Name	Ditto
UPC	887191584065

Agency

UL	E29179

Physical

Circuits (maximum)	8
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Hermaphroditic
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.858/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm

Obsolete

Downloaded from Arrow.com.

Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Ditto Hermaphroditic Crimp Housings	36877

Use with Part(s)

Description	Part Number
Ditto Hermaphroditic Crimp Terminals	36876

This document was generated on Apr 15, 2026

Obsolete

Downloaded from Arrow.com.