

**Part Number :** [1301020202](#)

**Product Description :** Super-Safeway Rubber Hand Lamp with 300W, Open End Vinyl Coated Guard with Reflector, with Switch and Receptacle, 7.62m (25.0') 16/3 SOOW

**Series Number :** 130102

**Status :** Obsolete

**Product Category :** Lamps and Lights

**Engineering Part Number :** 115USIA163



---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Obsolete
Category	Lamps and Lights
Series	130102
Description	Super-Safeway Rubber Hand Lamp with 300W, Open End Vinyl Coated Guard with Reflector, with Switch and Receptacle, 7.62m (25.0') 16/3 SOOW
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678860517

### Electrical

Lamp Wattage - Maximum	300W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

### Physical

Bulb Type	Incandescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	190.50mm (7.500")
Duty	Industrial
Guard Included	Yes
Guard Type	Insulated, Open End, Reflector
Height	371.35mm (14.620")
Lamp Type	A23
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel

Mounting Style	Hand Held
Outlet	Side
Packaging Type	Carton

---

This document was generated on May 19, 2026

Obsolete