Part Number : 1731121102
Product Description : FCT Slide Lock Post, #4-40 Thread, 12.70mm Thread Length, Tin-plated Steel
Series Number : 173112
Status : Active
Product Category : D-Sub Accessories
Engineering Part Number : F-SGV1/5-K142SN



Documents and Resources

Drawings

1731121102_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(a)-I per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Accessories
Series	173112
Description	FCT Slide Lock Post, #4-40 Thread, 12.70mm Thread Length, Tin-plated Steel
IP Rating	N/A
Magnetic	Yes
Product Name	FCT Products
Type	Backshell
UPC	191130516513

Physical

Accessory Type	Slide Lock Post
Material - Body	Steel
Net Weight	3.400/g
Packaging Type	Bag
Shell Size	1, 2, 3, 4, 5
Thread Size	4-40 UNC
Thread Type	Standard

Downloaded from Arrow.com.