


Rev	AWO #	Description	Date	Appr
-		RELEASED	6/22/17	


APPROVED: _____


DATE: _____ TITLE: _____











Positions: 06 thru 64
A= .100 [2.54] x No. of Spaces
B= .100 [2.54] x No. of Positions per Row + .021 [0.54]
C= .100 [2.54] x No. of Positions per Row + .205 [5.20]
D= .100 [2.54] x No. of Positions per Row – .039 [1.00]

SPECIFICATIONS:
Material:
Insulator: PBT, Glass reinforced, rated UL 94V–0
Insulator color: Black
Contacts: Phosphor Bronze
Plating:
Gold flash over Nickel underplate on contact area,
Tin over Nickel underplate on IDC tails
Electrical:
Current rating: 2 Amp
Contact resistance: 20 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 500 VAC
Temperature Rating:
–40°C to +105°C
Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	HR	6/22/17
CHECKED	MY	6/22/17
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.079 [2.00] FLAT CABLE IDC SOCKET
DUAL WIPE CONTACTS, W/FSR

SIZE	PART NO.	REV.
X	2FCS-C1-XX-SG-PB-FSR	-

REF: S00111C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.