

**Part Number :** 1204000228
**Product Description :** M12 Signal, A-Coded, M12 Push-Pull Ultra-Lock 2.0 Single-Ended Cordset, 5 Poles, Female (90°) to Pigtail, 22 AWG, Black TPU WSOR Cable, 1.0m (3.28') Length
**Series Number :** 120400
**Status :** Active
**Product Category :** Industrial Cable Assemblies
**Engineering Part Number :** Y05001B30M010

## Documents and Resources

### Drawings

1204000228_sd.pdf

STEP AP242

SOLIDWORKS

Creo

### Specifications

1204000001-P10.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Not Contained per D(2023)3788-DC (14 Jun 2023) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Industrial Cable Assemblies |
| Series | 120400 |
| Description | M12 Signal, A-Coded, M12 Push-Pull Ultra-Lock 2.0 Single-Ended Cordset, 5 Poles, Female (90°) to Pigtail, 22 AWG, Black TPU WSOR Cable, 1.0m (3.28') Length |
| IP Rating | IP67, IP69K |
| Product Name | M12 Signal Push-Pull,Ultra-Lock 2.0 (M12) |
| Type | Single Ended |
| UPC | 193264666188 |

### Agency

| | |
|---|---|
| CSA | LR6837 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 60V |

### Physical

| | |
|---|---|
| Cable Diameter | 5.50mm (.216") |
| Cable Length | 1.0m (3.28') |

Downloaded from Arrow.com.

| | |
|---|---|
| Color - Cable Jacket | Black |
| Connector End A | M12 Signal Push-Pull |
| Connector End B | Pigtail |
| Coupling Style | Push-Pull |
| Gender | Female-Pigtail |
| Keyway | A-Coded |
| LED Indicator | None |
| Material - Cable Jacket | TPU |
| Material - Connector Body | TPU |
| Material - Contact | Brass |
| Material - Coupling Nut | Polyamide |
| Material - O-Ring | Fluoro-elastomer |
| Material - Plating Mating | Gold |
| Net Weight | 56.980/g |
| Orientation | 90° to Pigtail |
| Poles | 5 |
| Temperature Range - Operating | -25° to +85°C |
| Wire/Cable Type | UL 21215, WSOR |
| Wire Size (AWG) | 22 |



Downloaded from Arrow.com.