



Color: white

Similar to illustration

| Technical data              |                                          |
|-----------------------------|------------------------------------------|
| Suitable                    | for wire cross-section 25 ... 35 mm²     |
| Marking method              | Thermal transfer                         |
| Delivery form               | Roll                                     |
| Delivery form configuration | 15 m/roll                                |
| Printing device             | Smart Printer (thermal transfer printer) |

| Physical data |          |
|---------------|----------|
| Depth         | 0.185 mm |

| Mechanical data  |                                         |
|------------------|-----------------------------------------|
| Mounting type    | Sliding on conductor                    |
| Shrink rate      | 2:1                                     |
| Smear resistance | in conjunction with 258-5005 Ink Ribbon |

| Material data        |                               |
|----------------------|-------------------------------|
| Color                | white                         |
| Material             | Polyolefin                    |
| UV resistance        | EN 60068-2-5:2010 Procedure B |
| Adhesive information | without adhesive              |
| Halogen-free         | Yes                           |
| Weight               | 426 g                         |
| Fire load            | 0 MJ                          |



| Environmental requirements      |                 |
|---------------------------------|-----------------|
| Ambient temperature (storage)   | +10 ... +25 °C  |
| Ambient temperature (operation) | -55 ... +125 °C |
| Relative humidity               | 45 ... 55 %     |

| Commercial data       |               |
|-----------------------|---------------|
| PU (SPU)              | 1 pcs         |
| Packaging type        | Box           |
| Country of origin     | DK            |
| GTIN                  | 4055143370318 |
| Customs tariff number | 39173200900   |

| Product Classification |                      |
|------------------------|----------------------|
| UNSPSC                 | 39121703             |
| eCl@ss 10.0            | 27-40-04-01          |
| eCl@ss 9.0             | 27-40-04-01          |
| ETIM 9.0               | EC001530             |
| ETIM 8.0               | EC001530             |
| ECCN                   | NO US CLASSIFICATION |

| Environmental Product Compliance |                        |
|----------------------------------|------------------------|
| RoHS Compliance Status           | Compliant,No Exemption |

| Downloads                                |                                                                                     |
|------------------------------------------|-------------------------------------------------------------------------------------|
| Environmental Product Compliance         |                                                                                     |
| Compliance Search                        |                                                                                     |
| Environmental Product Compliance 211-505 |  |

| Documentation                            |                                                                                                                        |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------|
| Operating Instructions                   |                                                                                                                        |
| 211-502 Information on printing material | <div>128.08.2020pdf1059.74 KB</div> |

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](https://www.wago.com)